

J1020- DRYING-K15

Precision is
our business



APPLICATION

The drying agent J1020-DRYING-K15 has a filling of about 12 g silica gel (orange).

It can be used in combination with the drying agent adaptor UV-J1002-ADA-DRYING-K15 to fit into the entrance optics UV-J1002 and UV-J1002-REG. There it is placed instead of the original drying agent tablet J1020-DRYING-K10.

It can be directly used as drying agent for the Solar Light broadband meter.

This big amount of drying agent allows a longer servicing free period for all instruments.

Physical data

Weight	0.012 kg
Size	35 mm (diameter) x 20 mm (length)
Material	transparent plastic
Thread	M18x1.5

CMS – Ing. Dr. Josef Schreder
Eggerstrasse 8
6322 Kirchbichl
AUSTRIA

Tel: 0043 / (0)5332 / 77056
Fax: 0043 / (0)5332 / 76692
E-Mail: info@schreder-cms.com